

CYCLESORB® FP2 Sales Specifications



CYCLESORB® FP2

DESCRIPTION

The **CYCLESORB® FP2 Service** is a mobile adsorption service combining adsorber and transport vessel for the treatment of corrosive liquid streams.

The **CYCLESORB® FP2**, pre-loaded, is delivered to a site and moved by forklift where required. The unit is operated until saturation of the activated carbon. A second unit is then delivered at the same time that the exhausted unit is picked to minimise transport.

Once the unit is returned to a **Chemviron Carbon** facility it is discharged of spent carbon, cleaned, checked and refilled with virgin or reactivated carbon.

The **CYCLESORB® FP2** comes complete with piping, valves and connections suitable for immediate connection to the stream to be treated. The frame for the unit allows it to be placed on a suitable flat and hard surface.

The liquid is pumped through the unit in a downflow direction. The outlet should be monitored periodically to check the activated carbon is achieving the treatment objective by regularly taking samples.

For larger flows or duties, a number of units can be used in parallel or series.

FEATURES

- A mobile adsorber service designed for **rapid and easy site installation** by forklift
- Corrosion resistant plastic materials
- Protective frame to avoid damage with regular transport and handling
- Adsorbers can be shipped with carbon such that **start up is immediate**
- Flexible service (rental) arrangements are available to meet short campaign or long term needs, **avoiding capital investment**
- No maintenance cost
- Carbon can be exchanged by simply changing units, **eliminating on site carbon transfer**
- **Sample connections** are fitted on the inlet and outlet piping for performance evaluation
- Spent carbon may be reactivated and recycled for reuse **to minimise waste**
- A range of **CYCLESORBS®** are available for larger flow applications
- Spare units are available in **Chemviron Carbon** production facility for change out

APPLICATIONS

Industrial

- Hydrochloric acid purification
- Aluminium chloride purification
- Chemical purification
- Waste water treatment
- Groundwater remediation with high chloride content


RECYCLING BY THERMAL REACTIVATION

Once granular activated carbon is saturated or the treatment objective is reached, it can be recycled, by thermal reactivation, for reuse. Reactivation involves treating the spent carbon in a high temperature reactivation furnace to over 800°C. During this treatment process, the undesirable organics on the carbon are thermally destroyed. Recycling by thermal reactivation is a highly skilled process to ensure that spent carbon is returned to a reusable quality. **Chemviron Carbon** operates Europe's largest reactivation facilities and daily recycles large quantities of spent carbon for a diverse range of customers. Recycling activated carbon by thermal reactivation meets the environmental need to minimise waste, reducing CO₂ emissions and limiting the use of the world's resource.

CARBON ACCEPTANCE

The return of the exhausted unit is subject to spent carbon acceptance procedures. For some new applications, a sample pot maybe supplied with the unit to allow a small bypass stream to be treated so a representative sample can be obtained for testing prior to return of the unit.

Equipment Bulletin



TECHNICAL DESCRIPTION

Carbon consumption, typical	5-50 tonnes/year
Carbon volume per adsorber	Approx. 900 kg, 2m ³
Flow rate, maximum	12 m ³ /h
Temperature, maximum ¹	50°C
Pressure, maximum ²	5 bar (gauge)
Rupture disk settings	5 barg at 20°C 4.7 barg at 50°C
Suspended solids ³	Up to 10 mg/l
Diameter	1.6 m
Connections – Main inlet/outlet	DN50 Kamlok male
Vessel materials	Polyethylene lined Fibre Reinforced Plastic
Piping material	polypropylene
Valves, type and materials	Ball, polypropylene
Rupture disc	Stainless Steel or carbon
Gasket for manhole	Neoprene or EPDM ⁴
Gaskets (pipeline)	EPDM
Footprint	1.64 x 1.64 m
Height – upright	2.3 m
Recommended clearance	2.5 m
Weight - Shipping (dry carbon)	1900 kg
Weight – shipping (drained)	2800 kg
Weight – operating (flooded)	4000 kg

¹ The inner lining resists to HCl 37 % at 50°C.

² The unit is not vacuum rated.

³ Depending on the flow and composition.

⁴ Different series have different gaskets.

SAFETY MESSAGE


Wet activated carbon preferentially removes oxygen from air. In closed or partially closed containers and vessels, oxygen depletion may reach hazardous levels. If workers are to enter a vessel containing carbon, appropriate sampling and work procedures for potentially low-oxygen spaces should be followed.

QUALITY

Each of our worldwide operations has achieved **ISO 9001** certification for their quality management system related to activated carbon. **Chemviron Carbon** guarantees the specifications against representative sampling.

PRESSURE DROP

Typical Pressure Drop
Cyclesorb FP2 12x40



CHEMVIRON CARBON

Chemviron Carbon, the European operation of Calgon Carbon Corporation, is a global manufacturer, supplier, and developer of granular activated carbon, innovative treatment systems, value added technologies, and services for optimising production processes and safely purifying the environment.

With our experience developed since the early years of the twentieth century, facilities around the world and a world-class team of over 1,200 employees, Calgon Carbon Corporation can provide the solutions to your most difficult purification challenges.

N.B. Chemviron Carbon reserves the right to change specifications without notice. All rights reserved for reproduction in part or in full without prior permission from Chemviron Carbon.

Visit our website at www.chemvironcarbon.com

ES1110 - E - 28.06.2006



CALGON CARBON CORPORATION

Corporate Headquarters
400 Calgon Carbon Drive
Pittsburgh, PA 15205, USA
Tel.: +1 (0) 412 787-6700
Fax: +1 (0) 412 787-6713

**Chemviron
Carbon**

European Operations of
Calgon Carbon Corporation
Zoning Industriel C de Feluy
B - 7181 Feluy, Belgium
Tél.: +32 (0) 64 51 18 11
Fax: +32 (0) 64 54 15 91

Your local office

